# WHO IS IT FOR?

#### Metrologists & process engineers

who need undisputable flow measurement data anywhere, anytime

#### **Hydrocarbon producers**

who require robust & reliable metering solutions

#### **Industrial producers**

who are serious about process optimisation

#### Flow meter manufacturers

who need a reliable flow computer to integrate their products with

# Gas transmission system operators

who want to be sure about their custody transfers and fiscal measurements

#### **Engineering companies**

who need to design redundant flow measurement systems at a moderate cost

#### Flow measurement professionals

who need to work with several types of existing equipment without problems

#### **System integrators**

who need heavy-duty solutions with a friendly price tag

#### **Energy professionals**

who want to keep tight account of energy consumption and  $\text{co}_2$  emission

See full specifications and try out UNIFLOW-200 at www.processcontrol.hu

## **OVERVIEW**

**UNIFLOW-200** is is an extremely reliable, user-friendly flow computer. A flexible and versatile instrument that satisfies all your flow measurement requirements.

Originally designed for hydrocarbon gas and liquid measurement, it's the perfect tool for fiscal measurements and custody transfers, but also works excellent in process applications where industrial gases, steam, or hot water are measured. UNIFLOW-200 is compatible with virtually all flow meters on the market. Eight meter runs handle up to eight different fluids with different types of flow meters, all in the same multi-run system. Measurements and calculations are based on the most recent international standards.

The expandable modular design provides interfaces for various metering equipments:

- Standard 4-20 mA
- RTD
- Pulse-frequency
- · Standard digital communications
- Digital inputs and outputs

UNIFLOW-200 connects to your gas chromatographs, mass and ultrasonic flow meters, and digital transmitters. It works both as a standalone unit and as a system component.

System communication interfaces:

- 3 serial ports sw-selectable RS232/RS485/RS422 (standard or Daniel Modbus protocol)
- 1 LAN port, 10/100 Ethernet (Modbus TCP protocol)
- 1 USB 1.1 port

Free software (UNIFLOW-200 Toolbox, Configurator and Remote Archive Uploader) makes installation, configuration, start-up, and everyday use easy and straightforward.

# PROCESS CONTROL UNIFLOW-200 MULTIFUNCTION FLOW COMPUTER

# SPECIFICATIONS & OVERVIEW

**Process Control Kft.** 

Déri Miksa utca 10. A/7. Nagytarcsa, 2142 Hungary +36 20 945 2477 info@processcontrol.hu www.processcontrol.hu



Multi-run & multi-station design: 8 meter runs and 4 station totalizations

**High-performance microprocessor** 

Galvanically isolated 1/0 points

Software calibrated I/O channels

**Smart transmitter interfaces** 

No potentiometers or batteries

Multiple Rs232/Rs485/Rs422 serial ports

10/100 Ethernet and USB port

Modbus TCP, Modbus, HART, Honeywell DE, US meter protocols

Configurable display

Reporting and data archiving

co2 emission calculation

Calculates all fluid properties according to relevant ISO, AGA, ASTM, GOST standards

Serial interfaces for gas chromatographs, mass and ultrasonic flow meters

Online configuration software

## **SPECIFICATIONS**

#### **Analog inputs**

Symmetrical inputs with galvanic isolation.

Input range	0/4-20 mA *
Accuracy	+/- 0.02 %
Input voltage drop	5.4 V max.
Potential diff. among inputs	50 V max.

#### 4-wire RTD inputs

Sensor type	PT100 **
Accuracy	+/- 0.03 °C
Wiring resist. incl. safety barriers	3 kΩ max.

#### Pulse-frequency input (incl. NAMUR)

Signal processing	without loss of pulses
Frequency range	0-10000 Hz
Input signal level	2 V-15 V
Signal form	square, unipolar
Inaccuracy of freq. meas.	0.001 % max.

#### **Digital inputs**

Potential-free contacts, open collector (transistor) and 24 V DC inputs can be accepted and used as static inputs, or pulse inputs (frequency: 100 Hz max.) without any further activity required from the user. Potential-free inputs are supplied with power from the circuit board (12 V DC, 6,8 k $\Omega$ ).

#### **Analog outputs**

Output channels with individual galvanic isolation.

Output range	0/4-20 mA *
Resolution	12 bits
Load	500 Ω max.

#### **Digital outputs**

Galvanically isolated open collector (transistor), overvoltage- and overcurrent-protected outputs.

Load	100 mA, 40 V max.

#### Field bus inputs

HART	point to point or multidrop connections, 24 V DC power supply
Honeywell DE	single or multivariable transmitters, 24 V DC power supply

#### **Digital communication**

RS232/RS422/RS485*	
Baud rate	1200-38400 bps
Protocol	Modbus (RTU, ASCII)
10/100 Ethernet	RJ45 (Modbus TCP)
USB port	1.1

#### **Operator panel**

3.5-inch QVGA 320×240 pixel backlit TFT color LCD display
Foil protected membrane keyboard

#### **EU conformity**

EC-type examination certificate	C€ marked
Le type examination certificate	- Cilialitea

#### **Uncertainty, MPE**

- Maximum permissible error (MPE) of the separate calculator on the calculation of quantities of gas, applicable to electronic calculators without uncertainty of the input channels: (OIML R 140:2007) +/-0.05 %.
- Maximum permissible error (MPE) of the separate calculator of gas volume conversion device including the uncertainty of the input channels: (EN 12405-1:2005) +/-0.2 %.

 Max. permissible error (MPE) of the separate calculator on the calculation of quantities of liquid (OIML R 117-1:2007) +/-0.03 %.

#### **Environment**

Operating temperature	-10-+60 °C
Operating humidity	10-90 % (non-condensing)
Storage temperature	-25−+70 °C

#### **Power requirements**

Dual power input	automatic switchover
Power inputs	
230 V AC +10 %, -15 %, 5	0-60 Hz
24 V DC (20-35 V)	
Power consumption	25 W max.
Transmitter power	1×24 V DC, 200 mA max.

#### **Dimensions**

Panel cut-out	186×91 mm
Case/min. cabinet depth	260/320 mm
Front panel	195×110 mm
Weight	4.3 kg

#### **Compliances & certificates**

**EN 12405, OIML R117, OIML R140, EC-type** certificate, available with **European CE** mark. Registered in the state register of metering equipment of the **Russian Federation**. **Registration number**: **58182–14**.

#### Standards in calculations

#### Flow meters

ISO 5167 (1991, 1998, 2003); EN 12405 (2005); AGA 3 (1990, 2012); AGA 7 (1996); AGA 9 (1998); GOST 8.563 (1997); GOST 8.586 (2005).

#### Gas

ISO 6976 (1995, 2015); ISO 20765-1 (2005); ISO TR 9464 (2008); AGA 5 (2009); AGA 8 (1985, 1992); AGA 10 (2003); GPA 2172 (2009); GOST 30319 (1996, 2015).

#### Dil

ASTM D 1250/API 2540/IP 200 (1980); MPMS Chapter 11.1 (2004); GPA TP-27 (2007); STO Gazprom 5.9 B1, B2, B3 (2007).

#### Water, steam

IAPWS-IF97

#### ı/o modules \*\*\*

ANI8	8 ch. 4-20 mA
РТ4	4 ch. рт100 **
ANI4PT2	4 ch 4-20 mA, 2 ch. рт100 **
PDIO484	4 ch. pulse input 8 ch. digital input 4 ch. digital output
AODIO484	4 ch. 4-20 mA output 8 ch. digital input 4 ch. digital output
нті4×15	4 loops to scan 15 HART PV/loop (multidrop) or 4 PCS HART transmitters (point to point) using HART protocol
DE4	2 PCs multivariable or 4 PCs single transmitters using DE protocol

#### **Supported flow meters**

Orifice, Compact Orifice, Venturi Tube, Nozzle, V-Cone, Annubar, Vortex, Turbine, Positive Displacement, Ultrasonic, Coriolis, Electromagnetic, Rotameter

#### **Supported fluids**

#### Hydrocarbons

natural gas, coke oven gas, blast furnace gas, crude oil, refined products, lubricating oil, UGC, SLH, WFLH, NGL & LPG

#### **Industrial** gases

air, nitrogen, oxygen, hydrogen, argon, carbon-dioxide, carbon-monoxide, ethylene, ammonium, propane, general gases

#### Liquids other than water

ethanol, мтве, етве, general liquids, two components liquid mixture

#### Water

water, water steam, water-glycol mixture - energy flow (heat transfer) calculation

- \* Software selectable.
- \*\* PT500 or PT1000 are also available.
- \*\*\* One UNIFLOW-200 MFC can accommodate up to 5 I/O boards in any combination.